

PM-360

Digital TENS (Transcutaneous electrical nerve stimulation)



- ◆ Dual channel, All Digital operation
- ◆ LCD Display
- ◆ Five TENS Modes: B (Burst), N (Normal), M (Modulation Rate & Width), S1, S2 (Modulation Width)
- ◆ Timer Adjustable, from 5 to 60 minutes and continuous (C), 5 minutes each step
- ◆ Patient compliance meter: Shows treatment times in hours
- ◆ System Includes: Stimulator, Lead Wires; 4 Self-Adhesive Reusable Electrodes, 9 Volt Battery, Low Battery Indicator Instruction Booklet, Hard Plastic Carrying case
- ◆ Optional: 9V AC Adapter and 9V Rechargeable Battery Kit Available

Technical Specifications


PM-360 (TENS Five Modes With Timer)

Channels:	Dual, isolated between channels
Wave Form:	Asymmetrical Bi-phasic square pulse
Pulse Amplitude:	Adjustable 0-80mA peak into 500 ohm load each channel, constant current
Pulse Frequency:	1Hz-160Hz (adjustable), 1Hz/step (1-20Hz), 5Hz/step (20-160Hz)
Pulse Width:	50μs - 260μs (adjustable), 10μs/step
Function Modes:	(B) Burst; (N) Normal; (M) Modulation; S1 Mode; S2 Mode; <ul style="list-style-type: none"> B: Burst Rate Adjustable 0.5-5Hz; Pulse width adjustable, 50-300 μs, Frequency Fixed 100Hz N: Normal Mode Pulse rate and width adjustable with continuous stimulation. M: Modulation Mode Pulse rate and width are automatically varied in a cycle pattern within 50% of its original setting. S1: Pulse width automatically varied in cyclic pattern over 10 seconds, then decreases over period of 4 seconds to 40% of its original setting. S2: Pulse width automatically varied in cyclic pattern over 10 seconds, then decreases over period of 4 seconds to 70% of its original setting.

Timer:	Adjustable from 5 to 60 minutes in 5 minute steps, or Continuous Mode
Patient Compliance Timer:	Unit store 60 sets of operation records.
Maximum Charge:	Unit stores 60 sets of operation records for a total time of 999 hours.
Power Source:	21 micro coulombs per pulse
Battery Life:	9 volt alkaline battery or similar rechargeable cell
Size:	70 hours average usage (alkaline)
Weight:	108mm(H) 61.5mm(W) 25mm(T)
	140grams (battery included)


All values have 10% +/- tolerance

Features and Controls




Front

1. Lead Connector
2. On/Off/Pause Control
3. Liquid Crystal Display
4. Mode Control
5. Set Control
6. Setting Increment Control
7. Setting Decrement Control
8. Intensity Increment Control
9. Intensity Decrement Control




Back

10. Belt Clip
11. Battery Strip
12. Battery Case



Side



Liquid Crystal Display

1. Intensity Level
2. Mode
3. Settings
4. Low Battery Indicator
5. Lock

Voice: 215.938.0200 ~ Toll-Free 1.800.472.9190 ~ Fax: 215.938-9309

www.ProMedSpecialties.com ~ 1800 Byberry Rd. Unit 905 ~ Huntingdon Valley, PA 19006 ~ USA