

ProM-507D


SD Tens-Deluxe Digital TENS Stimulator

NEW!


- ◆ Dual Channel (4-lead)
- ◆ Five Treatment Modes
- ◆ Fully Adjustable Pulse Rate and Width
- ◆ Unique Leather-like Protective Holster w/Belt Clip-Available in orange or black
- ◆ Easy-to-use Push Button Controls
- ◆ Parameter Lock and Compliance Monitor
- ◆ Ultra Hi-Tech Metallic Silver Finish
- ◆ Power ON/OFF Button for easy shut-off
- ◆ Treatment Timer (30, 60 minutes, or continuous)
- ◆ 3 year warranty
- ◆ Complete with 4 reusable electrodes, FDA safety compliant lead Wires, 9 Volt battery, carrying case and manual

Technical Specifications

Channel:	Dual, Isolated between Channels
Amplitude:	Adjustable, 0-80 mA peak each step
Output Voltage:	Adjustable, 0-40V peak
Waveform:	Asymmetrical biphasic square pulse
Pulse Rate:	Adjustable, 1~150 Hz, 1 Hz each step
Pulse Width:	Adjustable, 30~300µS, 10µS each step
Modes:	Five (Burst, Normal, Modulation, S1, S2)
Burst (B):	Burst Rate Adjustable 0.5~5 Hz Pulse width Adjustable 30~300µS Frequency fixed = 100 Hz
Pulse Rate Modulated:	Pulse rate varies to a maximum of 150 Hz from the control setting value. The variation is 40% or less of its original value
Pulse Width Modulation (S1):	Pulse width varies to a maximum of 300µS from the control setting value. The variation is 40% or less of its original value
Pulse Width Modulation (S2):	Pulse width varies to a maximum of 300µS from the control setting value. The variation is 70% or less of its original value
Timer:	30, 60 minutes and continuous
Power Supply:	One 9V battery
Size:	10.5cm (L) x 6.2cm (W) x 3.72cm (D)
Weight:	140 grams with battery



LIQUID CRYSTAL DISPLAY



Voice: 215.938.0200 ~ Toll-Free 1.800.472.9190 ~ Fax: 215.938-9309

www.ProMedSpecialties.com~ 1800 Byberry Rd. Unit 905 ~ Huntingdon Valley, PA 19006 ~ USA